


Microlens Array 10 x 10mm, 300µm Pitch, 2° Divergence, NIR II Coated



Microlens Arrays



Stock #21-153 3-4 DAYS

- 1 +

€805,00

ADD TO CART

Qty 1-10
€805,00
Qty 11+
€724,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
4.80

Substrate: [Fused Silica](#)

Coating: NIR II (750-1550nm)
Type: Lens Array
Wavelength Range (nm): 750 - 1550
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±2.0
Lens Profile: Spherical
Pitch (µm): 300.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 2.2
Thickness (mm): 0.90
Thickness Tolerance (mm): ±0.05
Type of Optics: Plano-Convex

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant