

[See all 42 Products in Family](#)

## Model 1103P, 2mW Linear Polarization, Lumentum HeNe Laser



Lumentum High Performance Helium-Neon Lasers



Stock #64-104 [CONTACT US](#)

- 1 + €1.145<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€1.145,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads



### General

10 **Warm-Up Time (minutes):**

Lumentum **Manufacturer:**

HeNe **Type of Laser:**

IIIa	Laser Class - CDRH:
------	---------------------

1103P	Model Number:
-------	---------------

## Physical & Mechanical Properties

N/A	Pointing Stability after Warm Up (mrad/°C):
-----	---

0.54	Weight (lbs):
------	---------------

9.50	Length of Laser Head (inches):
------	--------------------------------

Centered to Outer Cylinder: ±0.01" Parallel to Outer Cylinder: ±1.0 mrad	Static Alignment:
---	-------------------

From Cold Start, 25°: <0.1	Pointing Stability (mrad/°C):
----------------------------	-------------------------------

1.245	Diameter of Laser Head (inches):
-------	----------------------------------

## Optical Properties

500:1	Polarization:
-------	---------------

TEM <sub>00</sub>	Spatial Mode:
-------------------	---------------

632.80	Wavelength (nm):
--------	------------------

±3	Beam Diameter Tolerance (%):
----	------------------------------

±3	Beam Divergence Tolerance (%):
----	--------------------------------

Mean Power over 8 hrs: ±2.5	Maximum Drift:
-----------------------------	----------------

0.63	Beam Diameter (mm):
------	---------------------

1.30	Beam Divergence (mrad):
------	-------------------------

Red	Color:
-----	--------

>95%	Mode Purity (TEM <sub>00</sub> ):
------	-----------------------------------

## Electrical

2	Output Power (mW):
---	--------------------

30 Hz - 10 MHz 0.1%	RMS Noise:
---------------------	------------

730	Longitudinal Mode Spacing, Nominal (MHz):
-----	---

2.0	Minimum Output Power, TEM <sub>00</sub> (mW):
-----	---

## Hardware & Interface Connectivity

#11-380 (110/220V AC), #11-384 or #18-972 (12V DC), #11-385 (24V DC), #11-387 (110/220V AC)	Power Supply:
---	---------------

Free Space	Output Type:
------------	--------------

## Environmental & Durability Factors

-40 to +70	Operating Temperature (°C):
------------	-----------------------------

0 to 100%, non-condensing	Operating Humidity:
---------------------------	---------------------

-40 to +150	Storage Temperature (°C):
-------------	---------------------------

## Regulatory Compliance

Compliant	RoHS 2015:
-----------	------------

View	Certificate of Conformance:
------	-----------------------------

Compliant	REACH 241:
-----------	------------

## Product Details

110V or 220V power supplies sold separately. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993.

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

**Note:** Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

## Technical Information

### Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

