

SCHOTT GG395, 12.5mm Dia., 2mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-434** ☐ In Stock

-

1

+

€32,00

ADD TO CART

Qty 1-10
€32,00

Qty 11+
€28,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
395.00 ±6

Density (g/cm³): 2.55
Glass/Filter Number: SCHOTT GG395
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 480
Passband Limit 2 λ_{p2} (nm): 700
Index of Refraction n_d : 1.52
Spectral Transmittance t_p (%): 92
Stopband Limit λ_s (nm): 340
Surface Quality: 60-40
Transformation Temperature (°C): 538
Thickness (mm): 2.00 ±0.2
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
