

[See all 16 Products in Family](#)

Olympus Wide Field Tube Lens, 180mm Focal Length

See More by [Olympus](#)



Olympus Wide Field Tube Lens, #36-401

Stock **#36-401** 14 In Stock

-

1

+

€615^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€615,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
N5696600	Model Number:
Tube Lens	Type:
Olympus	Manufacturer:
Optical Properties	

180.00	Focal Length FL (mm):
1X	Magnification:
400 - 1000	Wavelength Range (nm):
26.5	Field Number (mm):
36.0	Entrance Pupil Diameter (mm):

Threading & Mounting

M41 x0.5	Mounting Threads:
----------	-------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:

Product Details

- High Numerical Aperture (NA) up to 1.45
 - Chromatic Aberration Correction from 400 - 1000nm
 - Uniform Image Flatness over Large FOVs
- Olympus X-Line Extended Apochromat Infinity Corrected Objectives (also referred to as the UPLXAPO series) are Olympus' next generation high performance objectives that simultaneously feature high numerical aperture (NA), broadband chromatic aberration correction, and excellent image flatness. The high numerical aperture (NA) allows for excellent light collection efficiency to better capture faint signals, enabling a shorter exposure time and higher contrast. The broad chromatic aberration correction compensates for the wavelength-dependent spatial shift of colors to achieve excellent color reproduction. These objectives also achieve high image flatness from the center to the edges of images over large fields of view (FOV), making them ideal for image stitching and quantitative image analysis. Olympus X-Line Extended Apochromat Infinity Corrected Objectives are used in demanding life science and clinical applications including pathology, fluorescence microscopy, multicolor or widefield fluorescence imaging, confocal or super resolution microscopy, and whole slide imaging.

Technical Information

	Stock #	A	B	C	D	E	F	G	WD
Olympus UPLXAPO 4X Objective	#14-905	31.89	-	-	15.4	15.4	28	4.7	13.0
Olympus UPLXAPO 10X Objective	#14-906	41.78	3.7	4.28	9.6	19.4	28	4.6	3.1
Olympus UPLXAPO 20X Objective	#14-907	44.28	3.39	2.88	10.2	18.6	28	4.8	0.61
Olympus UPLXAPO 40X Objective	#14-908	44.71	4.21	2.11	7.5	20.3	31.5	4.9	0.18
Olympus UPLXAPO 60X Oil Immersion Objective	#14-909	44.74	2.1	2.84	10	19.3	31.5	4.9	0.15
Olympus UPLXAPO 100X Oil Immersion Objective	#14-910	44.76	2.1	3.06	7.5	19.1	30.5	4.8	0.135

Technical diagram of an objective lens showing dimensions A through G and WD. A is the parfocal length (45.06 mm). B is the distance from the mounting flange to the front lens. C is the distance from the mounting flange to the rear lens. D is the distance from the mounting flange to the objective nose. E is the distance from the mounting flange to the objective base. F is the distance from the mounting flange to the objective tip. G is the distance from the mounting flange to the objective rear. WD is the working distance. The front lens diameter is Ø20.32 mm.