

[See all 16 Products in Family](#)

Olympus Wide Field Tube Lens, 180mm Focal Length

See More by [Olympus](#)



Olympus Wide Field Tube Lens, #36-401

Stock **#36-401** **14 In Stock**

1 €615⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | €615,00 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

N5696600 **Model Number:**

Tube Lens **Type:**

Olympus **Manufacturer:**

Optical Properties

| | |
|------------|--------------------------------------|
| 180.00 | Focal Length FL (mm): |
| 1X | Magnification: |
| 400 - 1000 | Wavelength Range (nm): |
| 26.5 | Field Number (mm): |
| 36.0 | Entrance Pupil Diameter (mm): |

Threading & Mounting

| | |
|----------|--------------------------|
| M41 x0.5 | Mounting Threads: |
|----------|--------------------------|

Regulatory Compliance

| | |
|------------------------|------------------------------------|
| Exempt | RoHS 2015: |
| View | Certificate of Conformance: |

Product Details

- High Numerical Aperture (NA) up to 1.45
- Chromatic Aberration Correction from 400 - 1000nm
- Uniform Image Flatness over Large FOVs

Olympus X-Line Extended Apochromat Infinity Corrected Objectives (also referred to as the UPLXAPO series) are Olympus' next generation high performance objectives that simultaneously feature high numerical aperture (NA), broadband chromatic aberration correction, and excellent image flatness. The high numerical aperture (NA) allows for excellent light collection efficiency to better capture faint signals, enabling a shorter exposure time and higher contrast. The broad chromatic aberration correction compensates for the wavelength-dependent spatial shift of colors to achieve excellent color reproduction. These objectives also achieve high image flatness from the center to the edges of images over large fields of view (FOV), making them ideal for image stitching and quantitative image analysis. Olympus X-Line Extended Apochromat Infinity Corrected Objectives are used in demanding life science and clinical applications including pathology, fluorescence microscopy, multicolor or widefield fluorescence imaging, confocal or super resolution microscopy, and whole slide imaging.

Technical Information

| | Stock # | A | B | C | D | E | F | G | WD |
|--|-------------------------|-------|------|------|------|------|------|-----|-------|
| Olympus UPLXAPO 4X Objective | #14-905 | 31.89 | - | - | 15.4 | 15.4 | 28 | 4.7 | 13.0 |
| Olympus UPLXAPO 10X Objective | #14-906 | 41.78 | 3.7 | 4.28 | 9.6 | 19.4 | 28 | 4.6 | 3.1 |
| Olympus UPLXAPO 20X Objective | #14-907 | 44.28 | 3.39 | 2.88 | 10.2 | 18.6 | 28 | 4.8 | 0.61 |
| Olympus UPLXAPO 40X Objective | #14-908 | 44.71 | 4.21 | 2.11 | 7.5 | 20.3 | 31.5 | 4.9 | 0.18 |
| Olympus UPLXAPO 60X Oil Immersion Objective | #14-909 | 44.74 | 2.1 | 2.84 | 10 | 19.3 | 31.5 | 4.9 | 0.15 |
| Olympus UPLXAPO 100X Oil Immersion Objective | #14-910 | 44.76 | 2.1 | 3.06 | 7.5 | 19.1 | 30.5 | 4.8 | 0.135 |

