

[See all 19 Products in Family](#)

Oryx® ORX-10GS-89S6M-C Mono 10GigE

See More by [Teledyne FLIR](#)



ORYX-10G-310S9C



Stock **#19-792** 1 In Stock

[Similar Cameras](#)

- 1 + €4.310⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€4.310,00 each

Volume Pricing	
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

Monochrome	Spectrum:
General	
Monochrome Camera	Type:
ORX-10GS-89S6M-C	Model Number:
FLIR	Manufacturer:
Onyx®	Camera Series:
Physical & Mechanical Properties	
60 x 60 x 64	Dimensions (mm):
386	Weight (g):
Full	Housing:
Sensor	
240MB	Image Buffer:
1"	Sensor Format:
8.90	Resolution (Megapixels):
93.00	Frame Rate (fps):
4,096 x 2,160	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
14.13 x 7.45	Sensing Area, H x V (mm):
Sony IMX255	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10/12 Bit	Pixel Depth:
5µs - 30s	Exposure Time:
71.57	Dynamic Range (dB):
GigE Vision	Machine Vision Standard:
Electrical	
12.6	Power Consumption (W):
Hardware & Interface Connectivity	
10GigE	Interface:
GigE interface with Screw Locks	Connector:
Power Supply: Power Supply Required and Sold Separately: USA: #19-803 Europe: #19-803 Japan: #19-803	

Korea: Not Available
China: [#19-803](#)

GPIOs:
2 opto-isolated inputs, 2 opto-isolated outputs, 2 non-isolated bi-directional

Synchronization:
Hardware Trigger (GPIO) or Software Trigger

Interface Port Orientation:
Back Panel

GPIO Connector Type:
12-pin Hirose (HR10)

Threading & Mounting

Mount:
C-Mount

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#19-804](#)

Environmental & Durability Factors

Operating Temperature (°C):
0 to +70

Storage Temperature (°C):
-30 to +60

Regulatory Compliance

Certificate of Conformance:
[View](#)

PRODUCT DETAILS

- 10GBASE-T (10GigE) Ethernet Interface
- 3.2 to 31 Megapixel Sony 4th Gen Pregius S Sensors
- Supports 4K60, 12-bit System Integration
- Tripod Adapter Built into Larger Oryx® Models



Teledyne FLIR IIS Oryx 10GigE High throughput, Award-winning camera designs

Reliably capture images at high speed

The **Oryx 10GigE** camera family supports transfer speeds of up to 10 Gbit/s enabling capture of 4K resolution, 12-bit images at speeds exceeding 60 FPS. Reliable image transfer at high bandwidth is further improved with Myricom bundles and packet resend feature. A range of sensor options offer resolutions from 3.2 Megapixel up to 31 Megapixel. Oryx features include IEEE1588 clock synchronization and full compatibility with several popular third-party software supporting GigE Vision. Oryx's 10GBASE-T interface is a proven and widely deployed standard that provides reliable image transfer at cable lengths over 50 meters on inexpensive CAT6A, and up to 30 meters on CAT5e.

Note: The ORX-10G-310S9 and ORX-10G-245S8 cameras require an F-Mount lens adapter (sold separately).

Features

- Color or monochrome sensors
- Various frame triggering options including up to 8 sets of 2-feature sequencer
- Pixel binning, decimation, ROI
- On camera image processing includes Gamma, LUT, and sharpness

Applications

- Stadium venues
- Site security
- Factory automation
- Traffic monitoring
- Inspection systems