

Pedestal Post, English, 12.7mm



Pedestal Post

Stock **#15-845** **4 In Stock**

€24⁷⁵

ADD TO CART

Volume Pricing

Qty 1-4	€24,75 each
Qty 5-9	€22,50 each
Qty 10+	€22,10 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English **Type:**

With 1/4-20 screw holes on the base **Note:**

Pedestal Post **Function:**

Physical & Mechanical Properties

Length (mm):
12.70

Construction:
Stainless Steel

Weight (kg):
0.06

Post Diameter (mm):
25.4

Base Diameter (mm):
31.5

Threading & Mounting

Mounting Threads:
8-32

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)





Product Details

- 1" Diameter Posts with Metric and English Mounting Hole Options
- Stainless Steel Construction for High Stability
- 0.5" - 4.0" Heights Available
- Refer to the Technical Information Tab to Find the Right Adapter for your Optical Mount and Application

Pedestal Posts and Accessories offer a stable way to mount optical components to a lab table with a consistent mounting height, providing predictable and repeatable mounting of components within an optical system. A variety of pedestal extenders and shim plates are available to ensure that the optical axis height is consistent for all mounted components. Pedestal Posts feature M4 x 0.7 or 8-32 tapped holes on the top surface, compatible with [TECHSPEC® Kinematic Mounts](#), [E-Series Kinematic Mounts](#), [Compact Mirror Mounts](#), and many other [optical mounts](#). M6 x 1.0 or 1/4"-20 tapped holes on the bottom surface make these Pedestal Posts directly mountable to Edmund Optics [stages](#) and [breadboards](#). For more compact table mounting, use the Compact Mounting Clamps ([#16-335](#)).

Note: Optical Mount Adapters are available to ensure consistent optical axis height and mounting hole compatibility with Edmund Optics' Optical Mounts. Refer to the Technical Information tab to find the right adapter for your application.

Technical Information

PEDESTAL POSTS AND ACCESSORIES					
Compatible Optic Mount	Optical Size	Mount Stock Number	Extension Length (mm)	Extender Stock Number for English Pedestals	Extender Stock Number for Metric Pedestals
 <p>Optic Component Mount</p>	50mm Dia.	#64-567	16.8	#16-321	#16-315
	2"/50.8mm Dia.	#64-569	16.8	#16-324	#16-587
 <p>Bar-Type Lens / Filter Holder</p>	1"/25.4mm Dia	#03-676	18	#16-325	#16-588
	2 axis: 2"/50.8mm Dia.	#62-957	8	#16-317	#16-311
	3 axis: 1"/25.4mm Dia.	#62-959	18	#16-222	#16-316
	5 axis: 1"/25.4mm Dia.	#13-776	18	#16-222	#16-316
	2"/50.8mm Dia.	#03-669	11	#16-323	#16-586
2"/50.8mm Dia.	#55-530	16	#16-320	#16-314	
 <p>Multi-Axis Adjustable Optic Mounts</p>	2 axis: 1"/25.4mm Dia.	#62-956	20.8	#16-460	#16-459
	2"/50.8mm Sq.	#54-995	11	#16-318	#16-312

<p>Retangular Bar Clamp</p>					
 <p>Filter Mount</p>	<p>2"/50.8mm Sq.</p>	<p>#54-997</p>	<p>14</p>	<p>#16-319</p>	<p>#16-313</p>
 <p>Multiple Filter Holder</p>	<p>30mm Dia.</p>	<p>#55-006</p>	<p>16</p>	<p>#16-320</p>	<p>#16-314</p>
 <p>Spring Mount Filter Holder</p>	<p>2"/50.8mm Sq.</p>	<p>#55-531</p>	<p>16</p>	<p>#16-320</p>	<p>#16-314</p>
 <p>Prism Mounts</p>	<p>25mm Cube</p>	<p>#55-013</p>	<p>18</p>	<p>#16-322</p>	<p>#16-316</p>
	<p>50mm Cube</p>	<p>#53-027</p>	<p>18</p>	<p>#16-325</p>	<p>#16-588</p>
 <p>Polarizer</p>	<p>1"/25.4mm Dia.</p>	<p>#55-011</p>	<p>18</p>	<p>#16-322</p>	<p>#16-316</p>
	<p>2"/50.8mm Dia.</p>	<p>#56-329</p>	<p>8</p>	<p>#16-317</p>	<p>#16-311</p>
 <p>Top Adjustment Kinematic Mount</p>	<p>1"/25.4mm Dia.</p>	<p>#55-456</p>	<p>14</p>	<p>#16-319</p>	<p>#16-313</p>
 <p>Gimbal Mount</p>	<p>2"/50.8mm Dia.</p>	<p>#55-000</p>	<p>11</p>	<p>#16-318</p>	<p>#16-312</p>