

TECHSPEC[®]Two Knob Stage & 12" Track Combination



One Knob Stage and Track Combination



Stock #59-338 14 In Stock

-

1

+

€348⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€348,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
English	Type:
Track & Two Knob Carrier Set	Note:

Physical & Mechanical Properties

Type of Movement:

Linear (X)	
62 x60	Stage Size (mm):
12	Travel (inches):
Black Anodized Aluminum	Construction:
Track: 0.1 Vernier Reading: 0.01	Graduation (inches):
5	Load Capacity, Normal (kg):
2	Load Capacity, Vertical (kg):
(6) 0.27" Thru on Track	S.H.C.S. C'bore:
0.1 - 0.25	Straight Line Accuracy (mm):
0.71	Travel Per Knob Rotation (inches):

Hardware & Interface Connectivity

Type of Drive:	
Rack and Pinion	

Threading & Mounting

(9) 1/4-20 on Carrier

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Carriers Feature One or Two Knobs, with English or Metric Mounting Hole Patterns
- Available with Both English and Metric Track Lengths
- Preassembled Common Carrier and Track Combinations are Available
- Vernier Scales of 0.01" or 0.1mm Resolution

TECHSPEC® Long Travel Rack and Pinion Stages are designed to allow for easy, long, linear adjustments while also maintaining precision and control. Available in English or Metric versions, these stages can be easily integrated into any system requiring controlled coarse positioning adjustments. Each track features an extruded dovetail design with a helical rack and pinion mechanism, ensuring smooth adjustments that can be locked with the included tension screw and Allen wrench. All TECHSPEC® Long Travel Rack and Pinion Stages feature a Vernier scale with a resolution of 0.01" or 0.1mm for accurate repeatable adjustments. Tracks feature either 1/4"-20 or M6 counter bored holes for mounting directly to a standard breadboard.

Note: Tracks and Carriers are available separately. English carriers can be used for Metric tracks and vice versa. For vertical configurations, use the Z-Axis Configuration Bracket (#11-165) which is compatible with both English and Metric Tracks and can be mounted to Metric or English bench plates/breadboards.

Technical Information



