

Variable Low Noise Current Amplifier



Stock **#59-178** 4 In Stock

-

1

+

€3.520⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-2	€3.520,00 each
Qty 3+	€3.256,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Remote Control:

Yes

Physical & Mechanical Properties

Weight (g):

320.00

Dimensions (mm):

Case Size: 150 x 55 x 44

Electrical

Transimpedance Gain (Ω):

10³ - 10¹¹ (adjustable in decade steps)

Bandwidth (-3 db):

500KHz max.	
	Bias Voltage: Adjustable by trimpot ±10V, max., 22mA
	Offset Adjustment: Adjustable by trimpot or external control voltage
	Input Current Noise (fA/√Hz): See datasheet

Hardware & Interface Connectivity

	Power Supply: Power Supply Required and Sold Separately. USA: #59-180 Europe: #59-180 Japan: Not Available Korea: Not Available China: #59-180
--	---

Environmental & Durability Factors

	Operating Temperature (°C): 0 to +60
--	--

Regulatory Compliance

View	Certificate of Conformance:
----------------------	------------------------------------

Product Details

- Convert Small Currents to Usable Voltages
- Variable Gain
- High Speed and Low Noise Designs

Current Amplifier Modules are current-to-voltage conversion devices used to amplify a small current from a photodiode or photomultiplier with very low noise. Low Noise and High Speed amplifiers are available with variable gain functionalities. The Low Noise amplifier is a two stage, low-noise amplifier with switchable AC/DC coupling, adjustable bias voltage offset, and a 10Hz lowpass filter. The High Speed model also features AC/DC coupling in addition to an adjustable offset for baseline correction, adjustable bias for use with fast photodiodes, and a switchable 10MHz and 1MHz low pass filters.

Note: [#59-178](#) and [#59-179](#) require specified power supplies.