

[See all 42 Products in Family](#)

## Power Supply for 1.5-2.0mW HeNe Laser, 12 VDC, Bare Wire Leads



L28 Series with CDRH Delay HeNe Laser Power Supply

Stock #11-384 [CONTACT US](#)

⊖ 1 ⊕ €350.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€350,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads



### General

OEM **Type:**

**Compatible Laser Models:**  
1101, 1101P, 1103, 1103P, 1122, 1122P

L23 Series **Model Number:**

**Compatible Laser Stock Number:**  
#62-718, #62-719, #62-720, #62-721, #64-103,  
#64-104

**Features:**

CDRH Delay (3-5 seconds)

**Physical & Mechanical Properties**

**Dimensions (inches):**

4.00 x 1.50 x 1.00

**Electrical**

**Output Power (W):**

8.33

**Input Current (A):**

3 (Max. Current Draw)

**Hardware & Interface Connectivity**

**Output Voltage (V):**

1700

**Output Current (mA):**

4.9

**Connector:**

High Voltage Alden Connector

**Input Voltage (V):**

10-14 DC

**Regulatory Compliance**

**Certificate of Conformance:**

[View](#)

**Product Details**

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

**Note:** Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

**Technical Information**

**Beam Expander Mounting Configurations**

Click on an item below to be brought to that item's product page.

