

Power Supply for 1.5-2.0mW HeNe Laser, AC, Bare Wire Leads



AC with Bare Leads HeNe Power Supply (#11-379, #11-380)

Stock **#11-380** 20+ In Stock

-

1

+

€474⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€474,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads



General

OEM

Type:

Compatible Laser Models:

1101, 1101P, 1103, 1103P

L92 Series

Model Number:

Compatible Laser Stock Number:

#62-718, #62-719, #64-103, #64-104

Features:	
CDRH Delay (3-5 seconds)	
Physical & Mechanical Properties	
Dimensions (inches):	
4.25 x 3.30 x 1.20	
Electrical	
Output Power (W):	
8.33	
Input Current (A):	
0.55/0.32	
Hardware & Interface Connectivity	
Output Voltage (V):	
1700	
Output Current (mA):	
4.9	
Connector:	
High Voltage Alden Connector	
Input Voltage (V):	
100/110/220 (AC)	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

