

[See all 8 Products in Family](#)

Wide Angle $\lambda/2$ Waveplate, 25.4mm Dia. 1550nm



Stock #29-818 **1 In Stock**

⊖ 1 ⊕ €2.130⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | €2.130,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Polymer Waveplate **Type:**

Physical & Mechanical Properties

17.8 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

+/- 0.13 **Dimensional Tolerance (mm):**

Optical Properties

±30 **Angle of Incidence (°):**

1550 **Design Wavelength DWL (nm):**

Polymer Film on **N-BK7** **Substrate:**

0.5 **Reflection (%):**

$\lambda/2$ **Retardance:**

60-40 **Surface Quality:**

$\leq \lambda/2$ @ 632.8nm **Transmitted Wavefront, RMS:**

$\leq \lambda/250$ @ 0 deg AOI, $\lambda/100$ at 30 deg **Retardance Tolerance:**

≤ 1 arcmin **Beam Deviation (arcmin):**

Threading & Mounting

6.35 **Mount Thickness (mm):**

Environmental & Durability Factors

0 - 40 **Operating Temperature (°C):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **REACH 241:**

Product Details

- Up To $\lambda/250$ Retardance Tolerances Out to 30° AOI
- Near Zero-Order Laminated Polymer Construction
- Ideal for Applications with Wide Acceptance Angles

Wide Angle Waveplates are designed to accept a large range of input angles, up to 30° AOI, with minimal retardance shift at non-zero angles of incidence. These waveplates are available with visible or NIR designed wavelengths of 532, 633, 1064 or 1550nm and with $\lambda/2$ or $\lambda/4$ retardance values. Featuring $\leq \lambda/250$ quarter-wave and $\leq \lambda/100$ half-wave retardance accuracies at the center, these waveplates are ideal for applications that require low sensitivity to AOI. Wide Field Waveplates are mounted and constructed with birefringent polymer on a N-BK7 substrate and coated with BBAR coatings.

Note: The fast axis is marked with a line.