


WinCamD-LCM-UV Beam Profiling Camera



#24-211 WnCamD-LCM Beam Profiler

Stock **#71-563** **1 In Stock**

⊖ 1 ⊕ €7.330⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€7.330,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

S-WCD-LCM-UV **Model Number:**

Contents of Kit:
Includes magnetic 1" ND and ND-UV filters (MagND-1, MagND-2, MagND-4, MagND-1-UV, MagND-2-UV, MagND-4-UV).

Physical & Mechanical Properties

46 x 46 x 20 **Dimensions (mm):**

Dimensional Accuracy:

±1µm

Optical Properties**Spectral Range:**

355 - 1150

Minimum Stimulation, Pulsed:

USB 2.0: 6.3 kHz USB 3.0: 12.6 kHz

Beam Diameter (µm):

55 (10 Pixels)

Sensor**Pixel Size, H x V (µm):**

5.5 x 5.5

Pixels (H x V):

2,048 x 2,048

Sensing Area, H x V (mm):

11.3 x 11.3

Sensor Format:

1"

Frame Rate:

60Hz

Electrical**Signal to Noise S/N Ratio (dB):**

2,500:1

Peak Noise (nW/cm²):

34 dB optical / 68 dB electrical

Threading & Mounting**Mount:**

8-32 thread, 8 mm deep

Regulatory Compliance**Certificate of Conformance:**[View](#)**Product Details**

- Designed for Use from 355 to 16000nm
- Compatible with Beam Diameters Down to 52µm
- Robust and Easy to Use Free Software [Provided](#)
- Measure Beam Wander, M, Divergence, and More

DataRay Camera Beam Profilers provide excellent solutions for beam analysis of both continuous wave and pulsed laser sources. Each beam profiler features an integrated CMOS sensor (IR profilers feature Microbolometer sensors) that eliminates comet trailing for higher resolution output and allows for update rates of 60+ Hz. Sensors are available with active sizes of 6.6, 11.3, and 25mm horizontals, enabling measurement of large beam diameters. DataRay Camera Beam Profilers have the added advantage of a free, robust software with analysis features such as M measurement, beam wander and logging, and instrument alignment. These profilers are USB3.0/2.0 powered and include a 3m flexible screw locking cable. Neutral density filters with optical densities of 1.0, 2.0, and 4.0 are included.