


Reflected (0.1875 - 12 lp/mm), Sinusoidal Target



Stock **#54-804** 1 In Stock

-

1

+

€1.330⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€1.330,00 each
Qty 5+	€1.264,20 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Reflected Sinusoidal	Type:
No	NIST Certification:

Physical & Mechanical Properties	
70 x48	Pattern Size (mm):

85 x200 ±nominal	Dimensions (mm):
0.18 ±nominal	Thickness (mm):
Semi-Matte, High Grain, Quality	Construction: Photographic Paper
Optical Properties	
0.1875 - 12	Frequency (lp/mm):
Float Glass	Substrate:
Grayscale Pattern: 0.2 - 1.2, ±0.02	Optical Density OD (Average):
<3	Harmonic Distortion (%):
Electrical	
60%	Modulation:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

• Designed for MTF Testing

• Determines Image Quality of Imaging Components

Sinusoidal patterns are designed specifically for evaluating the MTF of imaging lenses and other system components. This is accomplished by analyzing the ability of imaging components to reproduce the contrast of the sinusoidal target. MTF analysis is necessary when evaluating components to confirm that they meet design specifications and performance expectations. MTF evaluation is one of the best methods to determine overall image quality, not just absolute limitations. Implementation of MTF testing procedures can reduce costs by ensuring that neither under-specification nor over-specification occurs. The advantage of a sinusoidal target is that it relays image quality information over a full range of frequencies instead of only the maximum obtainable resolution. By using the different frequencies on the target, baselines can be established that directly relate to system requirements. The grayscales on the target are used as references for denoting the contrast levels of the sinusoidal frequencies.

Technical Information

