

SCHOTT NG9, 4.6 OD, 50mm Sq., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-070** **9 In Stock**

-

1

+

€99⁹¹

ADD TO CART

Volume Pricing	
Qty 1-10	€99,91 each
Qty 11-49	€87,55 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Neutral Density Filter

Physical & Mechanical Properties

50.0 x 50.0		Dimensions (mm):
50.00		Length (mm):
3.30 (nominal)		Thickness (mm):
50.00		Width (mm):
≤3		Parallelism (arcmin):
±0.2		Dimensional Tolerance (mm):

Optical Properties

4.6 ±0.07 @ 546nm		Optical Density OD (Average):
SCHOTT NG9		Glass/Filter Number:
Uncoated		Coating:
1.51		Index of Refraction (n _d):
60-40		Surface Quality:
0.003 ±0.00043% @ 546nm		Transmission (%):
400 - 700		Wavelength Range (nm):

Material Properties

470		Transformation Temperature (°C):
-----	--	----------------------------------

Regulatory Compliance

View		Certificate of Conformance:
Compliant		Reach 240:

PRODUCT DETAILS

- Tightly Controlled Transmission Specifications
- NG4, NG9, or NG11 Glass Types
- Specified Optical Densities from 0.15 to 5.0
- Provide Even Light Attenuation in the Visible Spectrum
- SCHOTT NG Gray Glass Also Available


SCHOTT NG Absorptive Neutral Density (ND) Filters consist of NG4, NG9, or NG11 SCHOTT glass types and provide even light attenuation through absorption in the visible spectrum. These filters are manufactured to achieve a specified optical density, ranging from 0.15 to 5.0, to simplify integration into optical systems. SCHOTT NG Absorptive Neutral Density (ND) Filters are available in a standard 50 x 50mm size and multiple filters can be stacked to achieve custom optical densities. Custom sizes from 5 to 160mm as well as custom optical densities or transmission values for specific wavelengths are available on request; for more information, visit our [Colored Glass Filter Manufacturing](#) capabilities webpage. [SCHOTT NG Gray Glass Filters](#) are also available.



Each filter lot is measured and thickness is adjusted to meet the specified transmission value at 546nm. Variations in filter lot performance can result in variations in nominal thickness; however, the transmission variations between lots will be minimal.

Filter Simulation Software

[Click here](#) to download SCHOTT's colored glass filter calculation program which can be used to calculate the internal transmittance and external transmission of each SCHOTT glass type. The program can simulate the performance of individual filters with user specified thickness or of stacked filters with varying glass types and thicknesses.

TECHNICAL INFORMATION





QUOTE YOUR SIZE

COMPATIBLE MOUNTS