

Thermopile Based Touchscreen Portable Laser Power Meter (Recertified 05-P)



Thermopile Based Touchscreen Portable Laser Power Meter, #34-515

Stock **#34-515-RCD-05P** RECERTIFIED **2 In Stock**

-

1

+

€796⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€796,00 each
Need More?	Request Quote

!

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

17

Operating Lifetime (hours):

5

Response Time (s):

Touch screen color LCD

Type of Display:

USB Port Available for Data Transfer		Note:
Physical & Mechanical Properties		
181.40	Length (mm):	
210	Weight (g):	
41.00	Width (mm):	
17.0	Depth (mm):	
3	Accuracy (%):	
Optical Properties		
190 - 20000	Wavelength Range (nm):	
0.19 - 20	Wavelength Range (μm):	
0.19 - 20μm	Spectral Range:	
0.248 - 2.5μm & 10.6μm	Calibrated Spectral Range:	
Sensor		
6 sec	Exposure Time:	
19mm Diameter	Maximum Sensor Size (mm):	
Electrical		
0.5W - 250W (average power)	Power Range:	
10	Noise Equivalent Power (mW):	
Hardware & Interface Connectivity		
USB Rechargeable Battery	Power Supply:	
Threading & Mounting		
8-32 threaded (x2)	Mounting Hole for Screw:	
Environmental & Durability Factors		
65	Maximum Temperature (°C):	
Regulatory Compliance		
View	Certificate of Conformance:	

PRODUCT DETAILS

- Small Portable Design with Touchscreen Display
- Computer and Software Not Required
- High Damage Threshold
- USB Rechargeable Battery

Touchscreen Portable Laser Power Meters feature LCD displays with touchscreen controls, the ability to adjust wavelength, brightness and screen orientation, and min/max display. Available in two designs, one as a silicon based sensor and the other an absorber, these portable power meters can transfer data to a computer for data logging via a mini USB port. The silicon sensor model (#34-514) features a folding body design with a click stop at 90 degrees, providing the unique ability of being placed on an optical table unmounted when oriented at 90 degrees. If the beam height is 78mm off the optical table, you can simply set the folded power meter directly onto the table. Both Touchscreen Portable Laser Power Meter models feature 8-32 mounting holes for table top mounting and rechargeable battery.

Note: Mini-USB cable not included.