

[See all 36 Products in Family](#)

## Triple Bandpass Blue-Green-NIR Filter M22.5



Stock #74-589 NEW 1 In Stock

- 1 + €381<sup>00</sup>

ADD TO CART

### Volume Pricing

Qty 1+	€381,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

**Full Width-Half Max FWHM Range (nm):**  
20nm, 20nm, 45nm ±10 nm

### General

Type:  
Triple Bandpass Mounted Imaging Filter

Model Number:  
TB475/550/850-22.5

### Physical & Mechanical Properties

Outer Diameter (mm):

24

2mm **Substrate Thickness (mm):**

## Optical Properties

Blue-Green-NIR **Color:**

40/20 **Surface Quality:**

≥85% **Transmission (%):**

468-483nm, 543-558nm, 835-865nm **Transmission Wavelength (nm):**

## Threading & Mounting

M22.5 x 0.50 **Filter Thread:**

5.2 **Mount Thickness (mm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

**Note:** Other filter threads are available upon request.