

[See all 157 Products in Family](#)

**TECHSPEC® Visible Plate Beamsplitter Kit, 25mm Diameter**



Stock #83-388 [CONTACT US](#)

- 1 + €540<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€540,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

**Note:**  
Beamsplitter-coated side is marked with a black dot

**Number of Filters:**  
5: [#47-240](#), [#68-385](#), [#45-852](#), [#68-403](#), [#48-398](#)

**Type:**  
Standard Beamsplitter

**Physical & Mechanical Properties**

**Construction:**  
Plate

## Optical Properties

### Coating Specification:

Surface 1: R/T  $\pm 5\%$  @ 550nm,  $R_{avg} \pm 10\%$  400 - 700nm

Surface 2: AR  $R_{avg} \leq 1\%$ ,  $R_{abs} \leq 2\%$  400 - 700nm

### Wavelength Range (nm):

400 - 700

## Regulatory Compliance

### Certificate of Conformance:

[View](#)

## Product Details

- Many Beamsplitting Ratios Available
- Visible and NIR Coating Options Offered
- Multi-Layer AR Coated Second Surface
- [C-Mounted Plate Beamsplitters](#) Also Available

TECHSPEC® Visible and NIR Plate Beamsplitters are ideal for dual magnification [imaging](#) systems and for combining low power [laser](#) beams. These beamsplitters offer the optimum combination of polished, high-quality optical-grade glass with minimum substrate thickness. The broadband dielectric coatings provide maximum throughput, are ideal for minimizing ghost images, and have much less energy loss than metallic coatings. TECHSPEC® Visible and NIR Plate Beamsplitters are coated on their back surfaces with a multi-layer anti-reflection (AR) coating, reducing back reflections to less than 1.0% for each wavelength range. Note that for easy identification, the coated side of the beamsplitter is marked with a black dot.

## Technical Information

