

TECHSPEC® 25mm Dia. Protected Gold Coated, Reflective Diffuser



Reflective Diffusers

Stock **#12-460** 3-4 DAYS

⊖ 1 ⊕ **€52,50**

ADD TO CART

Qty 1-10

€52,50

Qty 11+

€42,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 ±0.25

Coating:
Protected Gold (700-10000nm)

Coating Specification:

R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Grit: 120
Substrate:  Float Glass
Thickness (mm): 1.60 (nominal)
Type: Reflective Diffuser
Wavelength Range (nm): 700 - 10000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

