

TECHSPEC® 30mm Dia. Thin Mount, 8/32



TECHSPEC® Compact Mirrors & Lens Mounts

Stock **#13-794** [CONTACT US](#)

⊖ 1 ⊕ **€25,00**

ADD TO CART

Qty 1-4
€25,00
Qty 5+
€23,80
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Fixed

Size of Compatible Optics (mm):
30.0

Construction:
Black Anodized Aluminum

Type of Optics: Circular
Optic Holding Style: Requires C-Mount Circular Optic Mounts (30mm O.D.)
Clear Aperture CA (mm): 30
Compatible Post: 8/32
Tube System Compatibility: C-Mount Circular Optic Mounts
Centerline Height (mm): 25.4

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View