

TECHSPEC® 800 - 1200nm, 25.2 x 35.6mm, Dichroic Shortpass Filter Kit (9 Filters)



Stock #15-111 [CONTACT US](#)

- 1 + **€1.325,00**

ADD TO CART

Qty 1+
€1.325,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
25.2 x 35.6

Filters Included :
Cut-off Wavelengths: [800nm](#), [850nm](#), [900nm](#), [950nm](#),
[1000nm](#), [1050nm](#), [1100nm](#), [1150nm](#), [1200nm](#)

Length (mm):
35.60

Type:
Shortpass Filter

Width (mm): 25.20
Number of Filters: 9
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

