

**TECHSPEC®** 9mm Inner Single Optic Mount



TECHSPEC Multi-Element Inner Single Optic Mounts

Stock **#38-747** 3-4 DAYS

1 **€32,60**

ADD TO CART

|         |
|---------|
| Qty 1-4 |
| €32,60  |

|        |
|--------|
| Qty 5+ |
| €30,90 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:  
Fixed

Diameter of Compatible Optics (mm):  
9.0

Construction:  
Matte Black Anodized Aluminum (6061-T6)

|                                                         |
|---------------------------------------------------------|
| <b>Total Length (mm):</b><br>9.0                        |
| <b>Thread Type:</b><br>M29 x0.75                        |
| <b>Clear Aperture CA (mm):</b><br>8.0                   |
| <b>Function:</b><br>Optic Mount (Fixed)                 |
| <b>Max. Thickness of Compatible Optics (mm):</b><br>4.0 |
| <b>Min. Thickness of Compatible Optics (mm):</b><br>1.0 |
| <b>Edge Thickness of Compatible Optics (mm):</b><br>4.0 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |