

SURFACE: IMA
 IMA: 0.000 MM
SPOT DIAGRAM

45407
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD : :
 RMS RADIUS : 9.863
 SED RADIUS : 21.624
 SCALE BAR : 100



REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

45407
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 84.2336 μm
 DIFFRACTION LIMITED RANGE: 5.224 μm
 PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

CHROMATIC FOCAL SHIFT



TRANSVERSE RAY FAN PLOT

45407
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
 0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

45407
 TUE DEC 16 2008
 DATA FOR 0.4000 TO 0.7000 μm .
 SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

POLYCHROMATIC DIFFRACTION MTF