

SURFACE: IMA IMA: 0.000 MM

SPOT DIAGRAM

45410
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD : 1
 RMS RADIUS : 1.895
 GEO RADIUS : 2.759
 SCALE BAR : 10



EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

REFERENCE : CHIEF RAY

CHROMATIC FOCAL SHIFT

45410
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 452.2696 μm
 DIFFRACTION LIMITED RANGE: 121.804 μm
 PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



TRANSVERSE RAY FAN PLOT

45410
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 50.000 \mu\text{m}$.
 0.486 0.588 0.656

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

45410
 TUE DEC 16 2008
 DATA FOR 0.4000 TO 0.7000 μm .
 SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)