



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES





47699
TUE DEC 16 2008 UNITS ARE μm.
FIELD :
RMS RADIUS : 61.075
GD RADIUS : 157.889
SCALE BAR : 400

REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

47699
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 107.3916 μm
DIFFRACTION LIMITED RANGE: 6.823 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



47699
TUE DEC 16 2008
MAXIMUM SCALE: ± 500.000 μm.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

47699
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm.
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

EO Edmund
optics | worldwide

www.edmundoptics.com