





49313INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 26.341
GD RADIUS : 64.229
SCALE BAR : 200


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49313INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 132.7856 μm
DIFFRACTION LIMITED RANGE: 4.065 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT




TRANSVERSE RAY FAN PLOT

49313INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 200.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49313INK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm .
SURFACE: IMAGE



POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM