





49779INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 50.205
GD RADIUS : 126.496
SCALE BAR : 400


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49779INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 139.4965 μm
DIFFRACTION LIMITED RANGE: 9.445 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT




TRANSVERSE RAY FAN PLOT

49779INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 500.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49779INK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE



POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM