




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SHORTPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A                  | VALUE              |
|-------------------------|--------------------|
| CUT-OFF WAVELENGTH      | 900±2nm            |
| TRANSMISSION WAVELENGTH | 425 - 865nm        |
| REJECTION WAVELENGTH    | 960 - 1170nm       |
| TRANSMISSION            | >85                |
| SURFACE QUALITY         | 40-20              |
| COATING TYPE            | TRADITIONAL COATED |



|                        |    |        |   |
|------------------------|----|--------|---|
| THIRD ANGLE PROJECTION |    | TITLE  | M25.5 x 0.5, 900nm MOUNTED SHORTPASS FILTER |
| ALL DIMS IN            | mm | DWG NO | 66649                                       |
|                        |    |        | SHEET 1 OF 1                                |