





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**




LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CUT-ON WAVELENGTH	950nm
TRANSMISSION WAVELENGTH	985 - 2000nm
REJECTION WAVELENGTH	715 - 900nm
TRANSMISSION	>85
SURFACE QUALITY	40-20
COATING TYPE	TRADITIONAL COATED



THIRD ANGLE PROJECTION 		TITLE	M25.5 x 0.5, 950nm MOUNTED LONGPASS FILTER	
ALL DIMS IN	mm	DWG NO	66680	SHEET 1 OF 1