





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CUT-ON WAVELENGTH	700nm
TRANSMISSION WAVELENGTH	725 - 2000nm
REJECTION WAVELENGTH	535 - 660nm
TRANSMISSION	>85
SURFACE QUALITY	40-20
COATING TYPE	TRADITIONAL COATED



THIRD ANGLE PROJECTION



TITLE

M30.5 x 0.5, 700nm MOUNTED LONGPASS FILTER

ALL DIMS IN

mm

DWG NO

66690

SHEET 1 OF 1