




1. CONSTRUCTION: MOUNTED IN BLACK ANODIZED RING
2. COATING (APPLY ACROSS COATING APERTURE)

3. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
4. TRANSMITTED WAVEFRONT DISTORTION RMS@  $<1\lambda$
5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

 Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION 		TITLE  OD4, Ø50mm, 808nm, NOTCH FILTER		
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	Ø45.21	Ø45.21	ALL DIMS IN	mm	DWG NO	86704	SHEET 1 OF 1