





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	830nm
FULL WIDTH HALF MAX (FWHM)	3 ±1.0nm
MINIMUM TRANSMISSION	>80%
BLOCKING WAVELENGTH RANGE	700 - 821 & 839 - 1200nm
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED



THIRD ANGLE
PROJECTION

ALL DIMS IN

mm

EO[®] Edmund Optics[®]

TITLE

Ø12.5mm, 830nm CWL, 3nm FWHM, HARD
COATED LASER CLEAN-UP FILTER

DWG NO

68855

SHEET
1 OF 1