


Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

VIS 0° [425-675nm] Anti-Reflection Coating Performance
Typical Energy Density Limit: 5 J/cm² @ 532nm, 10ns
FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

Protected Silver Typical Coating Performance
 $R_{avg} = 96\%$ from 450 - 2000nm
FOR REFERENCE ONLY



COATING CURVE