

NOTES:




1. SUBSTRATE: FLOAT GLASS
2. WAVELENGTH RANGE: 400 - 700 nm

3. FINE GRIND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS
APPLY ACROSS CLEAR APERTURE

5. ROHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	41 x 63.5mm AR COATED FLOAT GLASS WINDOW	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	32740	SHEET 1 OF 1
SURFACE FLATNESS	4 - 6λ	4 - 6λ					
COATING	VIS	VIS					