





NOTES:

1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: Protected Silver (450-10000nm)  
R(AVG) >98% @ 450 - 800nm  
R(AVG) >98.5% @ 2000 - 10,000nm
- S2: NONE
3. EDGES SEAMED
4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO		TITLE	75 x 75mm Protected Silver, 4-6λ Mirror	
SURFACE QUALITY	60-40	N/A		DWG NO	36054	SHEET 1 OF 1
SURFACE FLATNESS	4 - 6λ	N/A				
CLEAR APERTURE	71.25 x 71.25	N/A				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN mm			