

NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: RAVG ≤0.5% @ 600 - 1050nm



5. Rohs Compliant







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø8.10	Ø8.10
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED
<u></u>		

				Edmund Optic	\$S®
THIRD ANGLE PROJECTION		TITLE	9mm DIA., 2mm THICK, NIR I COATED λ/4 N- BK7 WINDOW		
	ALL DIMS IN	mm	DWG NO	83465	SHEET 1 OF 1