



NOTES:

1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Aluminum (400-700nm)
R(AVG) >85% @ 400 - 700nm @ 45°

S2: NONE
3.

SEAMED EDGES
4. RoHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	N/A
SURFACE FLATNESS	4 - 6λ	N/A
CLEAR APERTURE	Ø 228.6 x 281.7	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION		Edmund Optics®		
TITLE		254 x 313mm, 4-6λ Mirror		
ALL DIMS IN	mm	DWG NO	32248	SHEET 1 OF 1