

NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <1 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: RABS ≤0.25% @ 880nm RAVG ≤1.25% @ 400 - 870nm RAVG ≤1.25% @ 890 - 1000nm



5. Rohs Compliant







PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø27.00	Ø27.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

			Edmund Optic	S®
HIRD ANGLE - PROJECTION	$\phi \Leftrightarrow$	TITLE	30mm DIA., 4mm THICK, VIS-NIR COA λ/4 N-BK7 WINDOW	TED
ALL DIMS IN	mm	DWG NO	48445	SHEET

SHEET 1 OF 1