



NOTES:

1. WAVELENGTH RANGE: 400 - 700nm:
2. COATING: UNCOATED
3. FINE GRIND SURFACE
4. ROHS COMPLIANT


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics**®

| | S1 | S2 |
|------------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE ACCURACY | COMMERCIAL POLISH | COMMERCIAL POLISH |
| SURFACE QUALITY | 80-50 | 80-50 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

| | | |
|--------|--------------------------------|--------------|
| TITLE | 5mm DIA. WHITE DIFFUSING GLASS | |
| DWG NO | 34467 | SHEET 1 OF 1 |