


NOTES:

1. SUBSTRATE MATERIAL:
FLOAT GLASS
2. ROHS COMPLIANT
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 50% R $\pm 5\%$ @ 550nm
50% T $\pm 5\%$ @ 550nm

S2: NONE


 EDGES CUT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

| REV. A | S1 | S2 | THIRD ANGLE PROJECTION  | | TITLE | 20 x 37mm, 50 R/50 T, PLATE BEAMSPLITTER | |
|------------------|-------------------|---------------------|--|----|--------|--|-----------------|
| SHAPE | PLANO | PLANO | ALL DIMS IN | mm | DWG NO | 31413 | SHEET 1 OF 1 |
| SURFACE QUALITY | 80-50 | 80-50 | | | | | |
| SURFACE FLATNESS | 4 - 6λ | 4 - 6λ | | | | | |
| BEVEL | PROTECTED AS NEED | PROTECTED AS NEEDED | | | | | |