

NOTES:

1. SUBSTRATE MATERIAL:
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)



S1 & S2: MgF2

R(avg) $\leq 1.75\%$ @ 400 - 700nm


3. FINE GROUND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
5. RoHS COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	 Edmund Optics®					
SHAPE	CONVEX	PLANO					EFL	-75
RADIUS	-38.8	∞					BFL	-76.7
SURFACE QUALITY	60-40	60-40			TITLE	12.5mm H X 25mm L X -75mm FL MgF2 COATED, CYLINDER LENS		
CLEAR APERTURE	11.50 X 24.00	11.50 X 24.00						
COATING APERTURE	11.50 X 24.00	11.50 X 24.00						
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	68074	SHEET 1 OF 1	