



NOTES:

1. SUBSTRATE MATERIAL:  
FLOAT GLASS
2. ROHS COMPLIANT
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 30% R  $\pm 5\%$  @ 550nm  
70% T  $\pm 5\%$  @ 550nm

S2: AR  $\frac{1}{4}\lambda$  MgF2 @ 550nm

 4. EDGES CUT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE FLATNESS	4 - 6λ	4 - 6λ
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE

35 x 35mm, 30 R/70 T, PLATE BEAMSPLITTER

DWG NO

45324

SHEET  
1 OF 1