## NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

\$1: 75% R ±5% @ 550nm 25% T ±5% @ 550nm

S2: NONE

4. EDGES CUT





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	80-50	80-50	
SURFACE FLATNESS	4 - 6λ	4 - 6λ	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	

_			
	THIRD ANGLE PROJECTION	$\phi \Box$	TITLE
	ALL DIMS IN	mm	DWG NO

(K)	Edi	mun	d	Ok	otic	S®
18 9	x 30mm	75 R/25 T	PLA	TF RF	TIII	TFR

1 OF 1

}	TITLE	18 X SUMMI, 75 R/25 I, PLATE BEAMSPLI	IIIEK
	DWG NO	47701	SHEET

46691