NOTES:


SURFACE FLATNESS


- 1. COATING (APPLY ACROSS CLEAR APERTURE)
 - \$1: R(abs) 70% ±5% @ 550nm
 R(abs) 70% ±10% @ 400 700 nm
 T(abs) 30% ±5% @ 550nm
 T(abs) 30% ±10%@ 400 700nm
 - S2: R(avg) <1.0% @ 400 700nm R(abs) <2.0% @400 - 700nm





ALL DIMS IN

mm









1λ

1λ

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

BO [®] Edmund Optics [®]		
TITLE	70R/30T, VIS, C-MOUNTED PLATE BEAMSPLITTER	
DWG NO	49686	Sheet 1 Of 1