




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SURFACE FLATNESS	2λ
PARALLELISM (arcmin)	≤3.5
CLEAR APERTURE (%)	≥90
EDGES	Chrome, Nickel, and Gold
WAVELENGTH RANGE (nm)	200 - 5500
WAVELENGTH RANGE (μm)	0.2 - 5.5
SOLDERABILITY	MIL-STD-883
RoHS	COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION		TITLE	5mm Diameter Uncoated, Metalized Sapphire Window		
		DWG NO	65894	SHEET 1 OF 1	