




NOTES:

- 1. MAIN MATERIAL: BLACK ANODIZED ALUMINUM
- 2. MIN DIA: 5mm
MAX DIA: 25mm
- 3. MAX EDGE THICKNESS: 2mm
- 4. RoHS: COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

THIRD ANGLE PROJECTION		TITLE	25mm, Bar-Type Lens/Filter Holder	
ALL DIMS IN	mm	DWG NO	55529	SHEET 1 OF 1