




FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING




BANDPASS FILTER

REV. A	VALUE
CENTER WAVELENGTH (CWL)	343nm \pm 1nm
FULL WIDTH HALF MAX (FWHM)	5.0 \pm 1nm
MINIMUM TRANSMISSION	\geq 85%
BLOCKING	200 - 1200nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED ALUMINUM RING
COATING TYPE	HARD COATED
DURABILITY	MIL-C-48497a, SEC 3.4.1
ENVIRONMENTAL	MIL-STD-810F, SEC 507.4

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	343nm CWL, 12.5mm Dia., Hard Coated OD4 5nm Bandpass Filter	
ALL DIMS IN	mm	DWG NO	39328	SHEET 1 OF 1