## NOTES:


- SUBSTRATE: UV GRADE FUSED SILICA


COATING (APPLY ACROSS COATING APERTURE): \$1 & \$2: UV-AR (250-425nm) R(ABS) ≤1.0% @ 250 - 425nm R(AVG) ≤0.75% @ 250 - 425nm R(AVG) ≤0.5% @ 370 - 420nm

3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <5 ARCSEC

4. FINE GRIND SURFACE

5. ROHS COMPLIANT





PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	]			Eamuna	<b>Optics</b> ®
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION		TITLE	25mm Dia., 2mm Thick, UV-AR Coated λ/10 Fused Silica Window	
SURFACE QUALITY	20-10	20-10					
CLEAR APERTURE	Ø20.00	Ø20.00					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	11880	SHEET 1 OF 1