


NOTES:


- 1. SUBSTRATE:
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)
NONE
- 3. SURFACE QUALITY: 60-40
- 4. WAVELENGTH RANGE: 350 - 2200 nm



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

<div><div>EO[®]</div><div>Edmund Optics[®]</div></div>			
THIRD ANGLE PROJECTION 		TITLE	50mm Diameter x 2mm Thickness, N-BK7 Glass Dome
ALL DIMS IN	mm	DWG NO	64497
			SHEET 1 OF 1