




NOTES:


- 1. SUBSTRATE: FLOAT GLASS
- 2. LINE PAIR PATTERN: 145lp/mm
- 3. PARALLELISM:
LINE TO LINE: ≤ 2 ARCSEC
PATTERN TO SUBSTRATE: $\pm 1^\circ$
- 4. COATING:
S1 & S2:
VACUUM DEPOSITED CHROME, OD > 3.0
- 5. RoHS: COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	1λ	1λ
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

 **Edmund Optics®**

THIRD ANGLE
PROJECTION



TITLE

1" x 1" (145 lp/mm), Ronchi Ruling

ALL DIMS IN

in

DWG NO

66350

SHEET

1 OF 1